


00902506 - CENTER-STRUT HEIGHT ADJUSTER

POWR-STICK OPERATION FOR RECTANGULAR BACKBOARD NO. 208 RECTANGULAR GLASS



Porter

WWW.PORTERATHLETIC.COM/FACILITY

BASKETBALL SPECIFICATION SHEET

B-902-506

00902506 POWR-STICK OPERATION FOR RECTANGULAR BACKBOARD

SEE B-200 FOR BACKBOARD AND GOAL OPTIONS

Porter
888-277-7778 PORTER@PORTERATHLETIC.COM
© COPYRIGHT 2018 PORTER ATHLETIC - ALL RIGHTS RESERVED

PROJECT NUMBER

PROJECT NAME

2/23/2018

00902506 - CENTER-STRUT HEIGHT ADJUSTER

POWR-STICK OPERATION FOR RECTANGULAR BACKBOARD
NO. 208 RECTANGULAR GLASS

SPECIFICATIONS

Height adjustment unit shall be designed for use with No. 900 Center-Strut® series ceiling suspended basketball backstop support systems to provide an adjustable, direct-mount (Center-Strut®) goal attachment system to eliminate any strain on the backboard should a player hang on the front mounted goal (conforms to the latest NCAA recommendation). Height adjustment units without the prescribed direct-mount goal feature will not be approved as equal. Height adjustment feature will allow goal height settings from 8'-0" to the official 10'-0" for use by all age groups. For use with No. 208 rectangular glass backboards.

Center unitized support frame shall be fabricated by dual, 2-3/16" square heavy-wall zinc plated guide tubes located on 11-3/16" centers. Ends of guide tubes shall be welded to heavy, formed mounting brackets. Heavy formed, die cut steel clamp assemblies (2) shall be provided for securing height adjustment assembly directly to a 6-5/8" O.D. center support structure (No. 900 Center-Strut® series basketball backstops). Outer dual slide tubes shall support heavy structural steel angle sections which extend downward to accept a direct-mount (Center-Strut®) goal mounting system. Slide tube assembly shall be provided with a heavy formed steel section to attach a special upper backboard support assembly to secure the unit to the upper two corners of the rectangular backboard on standard (5'-6") mounting centers.

Height adjustment unit shall incorporate a compact 115-volt, gear motor type linear actuator with 600 pound thrust capacity to raise and lower the goal height electrically. Motor shall draw 1.4 amps under full load. Integral limit switches shall provide automatic shut off at 8' and 10' goal heights. The motor shall be controlled by a Powr-Stick portable electric control. The Powr-Stick includes a rotary control switch with UP and DOWN positions and a center off position. The Powr-Stick easily plugs into a special receptacle mounted on the height adjuster frame from the floor. With an extension cord (not provided), the Powr-Stick connects to a standard 115-volt wall receptacle, eliminating the necessity for field wiring.

A height setting scale shall be located on the side of the unit to visually determine height settings from 8'-0" to 10'-0" in 3" increments.

Height adjustment frame shall be finished with one coat of flat black enamel. Hardware shall be furnished for mounting unit to a 6-5/8" O.D. vertical support tube.

WARRANTY

- Height Adjusters furnished with a 1-year limited warranty.